

AOR AR3000A "PLUS" Modifications

Introduction

The following modifications were originally developed by AOR (UK) Ltd as a result of popular requests by enthusiasts. They are described individually and can be carried out on that basis but when all modifications are done together they are collectively known as the "AR3000A PLUS" modifications.

The degree of difficulty in carrying out the modifications varies considerably. The discriminator modification simply involves the addition of one wire whereas the narrow AM filter uses very delicate surface mount components, fine wiring and the drilling of a hole in the main PCB. We therefore recommend that the instructions are read very carefully and tool kits inspected for suitability before attempting any modification. No test equipment should be needed for carrying out the modifications but a basic DVM is useful for fault finding. All modifications can be checked using off air signals and where applicable the SDU5000.

It is assumed before starting a modification that the AR3000 / AR3000A is in full working order and that no previous modifications have been carried out. All descriptions are based on the fact that the IF board has been removed from the set; this however is not necessary for some of the simpler modifications and partial removal is recommended by removing the five coaxial connectors on the front of the board and hinging the board on its remaining wiring loom over the back of the set.

In all the descriptions it is assumed that the front panel is facing towards you and is known as the "front" and the rear panel away from you and known as the "rear". Where colour of additional wires is given it is simply for clarity of description and is based on our original development of the modification. Components described are again based on those used in our original development and in most cases can be substituted; we have therefore only given recommended suppliers where the component is of a more specialised nature.

"Limited" support is offered by our technical department, time being valuable!

Written communication is discouraged in respect of these modifications due to the complexity of the subject matter. For answers to quick questions, phone 01773 880788. AOR (UK) LTD, 4E East Mill, Bridgefoot, Belper, Derbyshire DE56 2UA. England. *Thank you.*

WEFAX SATELLITE narrower switchable filter (1-3000)


The WEFAX custom modification has been designed to optimise the receiver's passband for reception of orbital weather satellites operating in the VHF band around 137.500 MHz and geostationary satellites operating in the UHF band around 1691 MHz. Ideally an IF bandwidth of 30-50 kHz is required for reasonable results, unmodified the AR3000 / 3000A is too narrow on NFM and too wide on WFM.

A small PCB is mounted on the IF PCB and holds both the original WFM filter for BAND2 & TV sound reception plus a new filter offering approximately 50 kHz bandwidth. The WFM filters are switched using an IC via a rear panel mounted slide switch (UP is narrow and DOWN is standard). A small component change is also carried out to ensure the squelch operates with the bandwidth switch in either position.

Of course you still require some form of data encoder such as the AOR WX2000 decoder/printer (no longer available as new) or a computer hardware/software package. For VHF reception a crossed dipole is quite adequate but a dish or yagi is required for UHF along with a LNA (low noise amplifier). The slide switch may be easily reached from the front of the set. The bandwidth is of course NOT selectable via computer control.

Using the accompanying diagrams and photographs build the small WEFAX PCB, the parts list being as follows

- 1 x Blank PCB 30.5 mm x 15.5 mm
- 1 x SMD 4066 IC quad switch
- 2 x SMD 10k resistors
- 1 x Murata SFE 10.7 MF filter, bandwidth 55 kHz Bonex part no 080125
- 1 x 300 mm green wire
- 1 x 300 mm blue wire
- 1 x 300 mm yellow wire
- 3 x 30 mm tinned wire leads
- 2 x wire links




Very carefully remove the existing WFM filter XF1 from the IF board and solder it to the new WEFAX PCB. Our experience tells us this is quite a fragile filter.

Add a 30 mm red supply feed wire to the hole in the IF PCB

alongside the XF1 position (see photograph).

Fit new WEFAX PCB to the IF board where the WFM filter XF1 was removed from.



The board should lean backwards with the filters towards the rear of the set (see photograph).

Solder the 3 wires to the IF board and the left hand edge of the new board to L7 transformer alongside.



Trim and solder the red supply wire to pin 14 of the 4066 IC on the new WEFAX board.

Locate and remove R57 4k7 resistor from the IF Board (see photograph) and replace with a 1k0 resistor.

Refit the IF board, twist the blue, yellow and green wires together and run them down the right hand edge of the IF board with the main loom. Follow the main loom towards the position of the new slide switch.

Using a sharp knife cut out the hole in the rear panel escutcheon next to the antenna socket to allow the fitting of a miniature DPDT slide switch. Drill out the mounting holes and fix the switch using 2 x M2x4 screws.

Trim and solder the blue, yellow and green twisted wires to one set of switch contacts connecting the yellow to the top connection, the blue to the middle connection and the green to the bottom connection.

The new switch now selects the standard WFM filter in the down position and the new narrower WEFAX filter in the up position. As a non technical test, tune to a WFM broadcast signal and switch in the narrower filter. You should hear slightly distorted reception as the incoming signal is deviated more than the filter bandwidth.

Refit the case halves and the modification is complete.

NARROW AM switchable filter (2-3000)


The narrow AM filter custom modification has been designed to optimise the receiver's passband for reception of short wave AM broadcast transmissions. Generally speaking on long and medium wave a 9 kHz channel spacing is used (in Europe) and a 5 kHz channel spacing for short wave. The standard AR3000A AM filter is 12 kHz as this permits reception of "offset" civil airband transmissions, the same filter is also used for NFM.

The modification adds a rear panel switchable narrow AM filter (the same switch as used for WEFAX switching - both are switched at the same time if both options are fitted), the filter specification bandwidth is 4.0 kHz but when fitted "in circuit" is actually wider than this. There is still a very worthwhile improvement which helps reduce BLOCKING when listening close-in to a strong transmission, heterodynes may also be reduced or removed

when listening to many transmissions. There is also a small increase in sensitivity over the standard filter by a few dB.



The additional narrow AM filter is fitted to the IF PCB with the data lines used to select the filter by diode switching in conjunction with the rear panel switch. The reception of NFM is still routed through the standard filter even when the narrow AM filter is selected.

When the narrow AM filter is selected the squelch closing position is affected. Instead of closing around 11 o'clock, it closes around 2 o'clock. This is not a problem as the squelch is usually left "open" when monitoring short wave broadcast transmissions.




The squelch characteristic is normal and unaffected when in the standard filter position. The bandwidth is of course NOT selectable via computer control.

The filter used is a CFW455IT, Bonex part no 080079. The filter sits on a blob of hot melt between L29 and the existing AM filter and is prepared in such a way that of it's three connections the input and output legs are extended and pass through holes in the PCB and the earth connection sticks out of the side of the hot melt and solders to the earth plane on the top side of the board.



Move the grey loop of wire on the underside of the IF board as far to the right of the PCB as possible and drill a hole 0.8 mm (through the board next to L29 on the IF PCB and suck the solder from the second hole if filled (see photograph).

Cut the input and output leg of the filter short and solder a 50 mm length of kynar wire vertically to each. Cut the middle leg of the three earth connections short and bend and cut the outer two to meet it. Solder all three together and add a 50 mm kynar earth wire



to exit horizontally to the filter towards the front of the set. The overall effect is that the filter should be able to sit low in it's blob of hot melt with its top level with the muRata SSB filter CFJ455K, it's two vertical wires through the prepared holes and the earth connection available to be soldered as close as possible to the earth land on the top of the PCB.

On the underside of the board add 2 x 1SS268 SMD diodes piggy backed onto 2 existing

Using a sharp knife cut out the hole in the rear panel escutcheon next to the antenna socket to allow the fitting of a miniature DPDT slide switch. Drill out the mounting holes and fix the switch using 2 x M2x4 screws.

Trim and solder the blue, yellow and green twisted wires to one set of switch contacts connecting the yellow to the top connection, the blue to the middle connection and the green to the bottom connection.

To test the unit tune to a broadcast AM station and switch the narrower filter in. You should hear a narrowing of tonal quality and a reduction in adjacent channel interference.

Refit the case halves and the modification is complete.

SDU5000 spectrum display compatibility (3-3000)

The SDU5000 is a new spectrum display unit designed to compliment the AR3000A (and other receivers). In order to provide compatibility, a custom modification has to be carried out to ensure the AR3000A will plug in and go!

Note: The AR3000 does not provide microprocessor compatibility with the SDU5000 so only basic facilities are available.

The modification to the AR3000A/3000 adds a rear panel BNC socket providing the required 10.7 MHz IF signal. The bandwidth is 10 MHz and gain is about 10dB compared to aerial input. A rear panel toggle switch provides AGC / mute for the SDU, normal is UP and active is down... the normal position being used most of the time. Of course the switch is NOT selectable via computer control.

Summary of SDU5000: The SDU5000 Spectrum Display Unit adds a variety of features to extend a receiver's capabilities, such as visually identifying new active frequencies and taking measurements. The SDU5000 may be used with a number of receivers which have a 10.7 MHz IF output and produces a bandwidth up to ± 5 MHz in 1 kHz increments with a resolution of 5 kHz or 30 kHz.


The SDU5000 remains compact due to the use of an internal 3.1" HQM simple matrix 16 colour LCD 192 dot x 210 dot. An external home colour television with video input may also been connected (PAL or NTSC).

In particular the AR3000A has been designed to provide best compatibility by communicating directly via the receiver's CPU via the RS232 port / SDU5000 COM1 ensuring the full potential of the SDU may be exploited.

Operation is extremely simple as the SDU5000 utilises an on screen menu system. The AR3000A frequency, mode & attenuator may be controlled from the SDU so that a displayed frequency may be easily monitored. When using the AR3000A, the cursor frequency is equal to the receiving frequency of the AR3000A, by using the cursor in the SDU, frequency and signal level can be read directly. This enables the SDU5000 to be used as a wide coverage spectrum monitor between 100 kHz to 2036 MHz with DDS providing an accuracy of 100ppm. Dynamic range is 50 dB with an acceptable input level between -10dBm to -90dBm with selectable gain control. The SDU-5000 has a multiple



processing function which displays Average Level, Peak Detection and Maximum Value Hold. These professional features are usually only available from expensive professional class spectrum analysers. The SDU may also be connected to a PC where all controls are accessible and display data can be downloaded for record and later analysis.

The SDU5000 operates from 12V DC @ 1A and a suitable mains power supply is provided along with the necessary connecting leads for the AR3000A.



To begin the modification add a 1N40148 diode to the IF board as shown in the photograph. Connect the cathode to the cathode of D7 and connect a 300 mm black wire to the anode.


Connect a 470R, 1/8W resistor between the emitter of Q7 and the junction of C45 and R29 (see photograph).




Short the emitter to the collector of Q9 with a small piece of tinned wire (see photograph).

Add one end of a 1000pF ceramic capacitor to the junction of L23 and C48. To the other end connect the inner of a 250 mm length of miniature 50R

coaxial cable. Connect the braid to the nearest suitable earth plane.



Insulate all fragile connections with a blob of hot melt and refit the board making sure that the coaxial lead and the black single wire exit from under the rear right corner of the board.



Connect a 150 mm red wire to the 9v output of regulator IC11 (right leg, see photograph) and run towards the back of the board.

Using a sharp knife cut out the rear panel escutcheon below the antenna socket and file away one of the flats to allow the fitting of a BNC socket.

Hot melt the coaxial cable along the bottom of the 25 way remote connector and trim and solder it to the new BNC socket.

Remove the DC socket and find the hole in the rear panel just below the DC socket hole, puncture the escutcheon and using it as a pilot hole drill a 6.5 mm(hole and fit a miniature SPDT toggle switch.

Trim and solder the black wire to the middle connection of the switch and trim and solder the red wire to the top connection of the switch. Refit the DC socket. Check the operation

of the modification with an SDU5000 or spectrum analyser refit the cases and the modification is complete.

Tape recorder compatibility (7-3000)

This custom modification enables the AR3000A to provide better compatibility with a range of "off the shelf" tape recorders. The AR3000A/3000 receiver uses a pair of Darlington transistors for tape motor On/Off control. While this is suitable for many machines, some require independent relay contacts.

The modification consists of a small internally fitted double pole slave relay driven by the switching transistors. One pair of relay contacts feed back to the AUX socket via a 10 OHM resistor (to prevent relay sticking) and provides independent relay contacts not referenced to ground. The second pair of contacts feed audio to the AUX socket when the squelch is open with a high value resistor preventing noise pick-up when the contact is open. Constant audio is still fed to another pin of the AUX socket taken from a point before the relay (audio is permanently fed so that commercial users may decode CTCSS signals without encountering any squelch rise time). This makes the tape output modification ideally suited for direct DC switching of tape motors (not mains!) and for voice activated systems.

AUX SOCKET

Pin2: Ground

Pin4: Constant audio out

Pin5: Squelch operated audio output for VOX

Pin6: Relay switch contact

Pin7: Relay switch contact

A standard tape lead CR400 is available as an option terminating in 3.5 mm mono plugs for audio and a 2.5 mm plug for tape motor control.

Begin the modification by removing the DC socket and aux socket.

Remove the brown and white wires from pins 6 and 7 of the aux socket and connect the white wire to a +ve 12v supply on the rear of the power socket or pin 3 of the aux socket if available (this was not fitted on earlier models)

Remove the 220k resistor from pins 4 and 5 and connect a 100k resistor from pin 5 to pin 2 (gnd)

Connect a pair of 100 mm blue wires to pins 6 and 7 and a pair of 100 mm yellow wires to pin 4 and 5.

Refit the aux socket and DC socket

Using a 12v double pole relay with internal diode protection trim and solder the pair of blue wires to one pair of normally open contacts. Fit a 10(1/8W resistor in series to prevent the relay contacts sticking.


Trim and solder the yellow pair of wires to the second pair of normally open contacts on the relay.

Connect the brown wire removed from the aux socket to the +ve coil connection on the relay and connect a black wire between the -ve connection and an earth connection (remote socket PCB)

Stick the relay to the inside of the rear panel, check operation of the switching and refit the case halves. That completes the modification.

Discriminator output (9-3000)

This custom modification provides an output to the rear panel AUX socket taken directly from the FM MC3357 IC. This ensures the best compatibility with specialist data receivers used on the VHF bands for decoding pagers etc.





AUX SOCKET


Pin2: Ground

Pin1: Discriminator output


On the underside of the IF PCB solder a 300 mm black wire to pin 9 of IC! (see photograph) and refit the board.

Remove the DC socket and aux socket. Connect the black wire to pin 1 of the aux socket and refit both sockets. Test the operation and refit the case halves. That completes the modification.






Unmodified I.F. PCBs




00.





MAIN UNIT PARTS LAYOUT

(iv)

AR-3000 IF PCB A (P-8901D)








14

P1L 2nd OSC UNIT





CPU/LCD UNIT

NO.	DESCRIPTION	QTY	REMARKS
1	IC 1 (CPU)	1	
2	IC 2 (CPU)	1	
3	IC 3 (CPU)	1	
4	IC 4 (CPU)	1	
5	IC 5 (CPU)	1	
6	IC 6 (CPU)	1	
7	IC 7 (CPU)	1	
8	IC 8 (CPU)	1	
9	IC 9 (CPU)	1	
10	IC 10 (CPU)	1	
11	IC 11 (CPU)	1	
12	IC 12 (CPU)	1	
13	IC 13 (CPU)	1	
14	IC 14 (CPU)	1	
15	IC 15 (CPU)	1	
16	IC 16 (CPU)	1	
17	IC 17 (CPU)	1	
18	IC 18 (CPU)	1	
19	IC 19 (CPU)	1	
20	IC 20 (CPU)	1	
21	IC 21 (CPU)	1	
22	IC 22 (CPU)	1	
23	IC 23 (CPU)	1	
24	IC 24 (CPU)	1	
25	IC 25 (CPU)	1	
26	IC 26 (CPU)	1	
27	IC 27 (CPU)	1	
28	IC 28 (CPU)	1	
29	IC 29 (CPU)	1	
30	IC 30 (CPU)	1	
31	IC 31 (CPU)	1	
32	IC 32 (CPU)	1	
33	IC 33 (CPU)	1	
34	IC 34 (CPU)	1	
35	IC 35 (CPU)	1	
36	IC 36 (CPU)	1	
37	IC 37 (CPU)	1	
38	IC 38 (CPU)	1	
39	IC 39 (CPU)	1	
40	IC 40 (CPU)	1	
41	IC 41 (CPU)	1	
42	IC 42 (CPU)	1	
43	IC 43 (CPU)	1	
44	IC 44 (CPU)	1	
45	IC 45 (CPU)	1	
46	IC 46 (CPU)	1	
47	IC 47 (CPU)	1	
48	IC 48 (CPU)	1	
49	IC 49 (CPU)	1	
50	IC 50 (CPU)	1	
51	IC 51 (CPU)	1	
52	IC 52 (CPU)	1	
53	IC 53 (CPU)	1	
54	IC 54 (CPU)	1	
55	IC 55 (CPU)	1	
56	IC 56 (CPU)	1	
57	IC 57 (CPU)	1	
58	IC 58 (CPU)	1	
59	IC 59 (CPU)	1	
60	IC 60 (CPU)	1	
61	IC 61 (CPU)	1	
62	IC 62 (CPU)	1	
63	IC 63 (CPU)	1	
64	IC 64 (CPU)	1	
65	IC 65 (CPU)	1	
66	IC 66 (CPU)	1	
67	IC 67 (CPU)	1	
68	IC 68 (CPU)	1	
69	IC 69 (CPU)	1	
70	IC 70 (CPU)	1	
71	IC 71 (CPU)	1	
72	IC 72 (CPU)	1	
73	IC 73 (CPU)	1	
74	IC 74 (CPU)	1	
75	IC 75 (CPU)	1	
76	IC 76 (CPU)	1	
77	IC 77 (CPU)	1	
78	IC 78 (CPU)	1	
79	IC 79 (CPU)	1	
80	IC 80 (CPU)	1	
81	IC 81 (CPU)	1	
82	IC 82 (CPU)	1	
83	IC 83 (CPU)	1	
84	IC 84 (CPU)	1	
85	IC 85 (CPU)	1	
86	IC 86 (CPU)	1	
87	IC 87 (CPU)	1	
88	IC 88 (CPU)	1	
89	IC 89 (CPU)	1	
90	IC 90 (CPU)	1	
91	IC 91 (CPU)	1	
92	IC 92 (CPU)	1	
93	IC 93 (CPU)	1	
94	IC 94 (CPU)	1	
95	IC 95 (CPU)	1	
96	IC 96 (CPU)	1	
97	IC 97 (CPU)	1	
98	IC 98 (CPU)	1	
99	IC 99 (CPU)	1	
100	IC 100 (CPU)	1	

RR-3000B CPU/LCD-UNIT.

NO.	DESCRIPTION	QTY	REMARKS
1	IC 1 (CPU)	1	
2	IC 2 (CPU)	1	
3	IC 3 (CPU)	1	
4	IC 4 (CPU)	1	
5	IC 5 (CPU)	1	
6	IC 6 (CPU)	1	
7	IC 7 (CPU)	1	
8	IC 8 (CPU)	1	
9	IC 9 (CPU)	1	
10	IC 10 (CPU)	1	
11	IC 11 (CPU)	1	
12	IC 12 (CPU)	1	
13	IC 13 (CPU)	1	
14	IC 14 (CPU)	1	
15	IC 15 (CPU)	1	
16	IC 16 (CPU)	1	
17	IC 17 (CPU)	1	
18	IC 18 (CPU)	1	
19	IC 19 (CPU)	1	
20	IC 20 (CPU)	1	
21	IC 21 (CPU)	1	
22	IC 22 (CPU)	1	
23	IC 23 (CPU)	1	
24	IC 24 (CPU)	1	
25	IC 25 (CPU)	1	
26	IC 26 (CPU)	1	
27	IC 27 (CPU)	1	
28	IC 28 (CPU)	1	
29	IC 29 (CPU)	1	
30	IC 30 (CPU)	1	
31	IC 31 (CPU)	1	
32	IC 32 (CPU)	1	
33	IC 33 (CPU)	1	
34	IC 34 (CPU)	1	
35	IC 35 (CPU)	1	
36	IC 36 (CPU)	1	
37	IC 37 (CPU)	1	
38	IC 38 (CPU)	1	
39	IC 39 (CPU)	1	
40	IC 40 (CPU)	1	
41	IC 41 (CPU)	1	
42	IC 42 (CPU)	1	
43	IC 43 (CPU)	1	
44	IC 44 (CPU)	1	
45	IC 45 (CPU)	1	
46	IC 46 (CPU)	1	
47	IC 47 (CPU)	1	
48	IC 48 (CPU)	1	
49	IC 49 (CPU)	1	
50	IC 50 (CPU)	1	
51	IC 51 (CPU)	1	
52	IC 52 (CPU)	1	
53	IC 53 (CPU)	1	
54	IC 54 (CPU)	1	
55	IC 55 (CPU)	1	
56	IC 56 (CPU)	1	
57	IC 57 (CPU)	1	
58	IC 58 (CPU)	1	
59	IC 59 (CPU)	1	
60	IC 60 (CPU)	1	
61	IC 61 (CPU)	1	
62	IC 62 (CPU)	1	
63	IC 63 (CPU)	1	
64	IC 64 (CPU)	1	
65	IC 65 (CPU)	1	
66	IC 66 (CPU)	1	
67	IC 67 (CPU)	1	
68	IC 68 (CPU)	1	
69	IC 69 (CPU)	1	
70	IC 70 (CPU)	1	
71	IC 71 (CPU)	1	
72	IC 72 (CPU)	1	
73	IC 73 (CPU)	1	
74	IC 74 (CPU)	1	
75	IC 75 (CPU)	1	
76	IC 76 (CPU)	1	
77	IC 77 (CPU)	1	
78	IC 78 (CPU)	1	
79	IC 79 (CPU)	1	
80	IC 80 (CPU)	1	
81	IC 81 (CPU)	1	
82	IC 82 (CPU)	1	
83	IC 83 (CPU)	1	
84	IC 84 (CPU)	1	
85	IC 85 (CPU)	1	
86	IC 86 (CPU)	1	
87	IC 87 (CPU)	1	
88	IC 88 (CPU)	1	
89	IC 89 (CPU)	1	
90	IC 90 (CPU)	1	
91	IC 91 (CPU)	1	
92	IC 92 (CPU)	1	
93	IC 93 (CPU)	1	
94	IC 94 (CPU)	1	
95	IC 95 (CPU)	1	
96	IC 96 (CPU)	1	
97	IC 97 (CPU)	1	
98	IC 98 (CPU)	1	
99	IC 99 (CPU)	1	
100	IC 100 (CPU)	1	





Price list for customising existing AR3000A & AR3000 receivers

Full details of custom modifications are available in a separate sales booklet. If you select only a single modification from any group then the higher price is applied as the cases and PCBs need to be removed just for one job, savings can be made if several modifications are carried out at the same time. **Prices £ Pound Sterling E&OE.**

Group A

If more than one group "A" modification is selected then the lower price is applied to each modification as the unit will already have been stripped making work more cost effective.

Group B

There is no lower price available for group "B" as work is time consuming.

Group C

If either a group "A" or group "B" modification is selected then the lower price is applied to group "C" modifications as the unit is already stripped making work cost effective.

Group A (lower price applies if more than one group A modification is carried out)

1-3000	WEFAX switched WFM filter	£39.95 inc VAT	/	34.95
2-3000	Narrow AM switched filter	£39.95 inc VAT	/	34.95
3-3000	SDU 10.7 MHz IF & switch	£39.95 inc VAT	/	34.95
4-3000	10.7 MHz I.F. only	£35.95 inc VAT	/	32.95
5-3000	45 MHz I.F. for commercial use	£39.95 inc VAT	/	34.95

Group B (no lower price available)

6-3000	S-meter output	£19.95 inc VAT	/	
7-3000	Tape recorder switching	£19.95 inc VAT	/	

Group C (lower price applies if a group A or B modification is also carried out)

8-3000	Microprocessor reset switch	£14.95 inc VAT	/	9.95
9-3000	Discriminator output for decoder	£14.95 inc VAT	/	4.95
10-3000	Encoder change for AR3000A only	£19.95 inc VAT	/	14.95
11-3000	RS232 switch for AR3000 only	£19.95 inc VAT	/	14.95

Carriage on modified units

Return carriage using insured courier Parcel Force PF24 (next working day) is typically £10.00 inc VAT. We are also able to collect your receiver from your home or place of work using our PF24 courier facility. Pack the parcel well in a carton box, write our name & address clearly on the outside of the carton and give us a call... we will arrange the rest. The charge is £22.00 for the round trip.

Many other accessories and custom made leads are available for the AR3000A/3000 (leads are hand made), please phone for a quote.

***** It is unlikely that we will be able to offer the modification service on a while you wait basis, the work should usually be carried out within one working week. Please feel free however to phone and discuss fitting in our workshop.**

If you are currently looking for a custom modified AR3000A then the *AR3000A PLUS* will save money compared to the lowest tariff charges - please see overleaf.
Perhaps now is the time to consider upgrading your current equipment.



Customised AR3000A receiver

Distributed by AOR (UK) LTD

The *AR3000A+ (PLUS)* is the result of popular request by enthusiasts and carries several custom modifications which have been developed and implemented in our UK workshop. A summary of the additions and operation follows:

WEFAX SATELLITE narrower switchable filter

The WEFAX custom modification has been designed to optimise the receiver's passband for reception of orbital weather satellites operating in the VHF band around 137.500 MHz and geostationary satellites operating in the UHF band around 1691 MHz. Ideally an I.F. bandwidth of 30 - 50 kHz is required for reasonable results, unmodified the AR3000A is too narrow on NFM and too wide on WFM.

Of course you still require some form of data decoder such as the AOR WX2000 decoder/printer (no longer available as new) or a computer hardware / software package. For VHF reception a crossed dipole is quite adequate but a dish or yagi is required for UHF along with a LNA (low noise amplifier).

NARROW AM switchable filter

The narrow AM filter custom has been designed to optimise the receiver's passband for reception of short wave AM broadcast transmissions. Generally speaking on long and medium wave a 9 kHz channel spacing is used (in Europe) and a 5 kHz channel spacing for short wave. The standard AR3000A AM filter is 12 kHz as this permits reception of "offset" civil airband transmissions, the same filter is also used for NFM. The modification adds a rear panel switchable narrow AM filter (the same switch as used for WEFAX switching - both are switched at the same time), the filter specification bandwidth is 4.0 kHz but when fitted "in circuit" is actually wider than this. There is still a very worthwhile improvement which helps reduce BLOCKING when listening close to a strong transmission, heterodynes may also be reduced or removed when listening to many transmissions. There is also a small increase in sensitivity over the standard filter by a few dB.

SDU5000 spectrum display "ready"

A new spectrum display unit designed to compliment the AR3000A, in order to provide compatibility, a custom modification has to be carried out to ensure the AR3000A+ (*PLUS*) is ready to go!

Summary of SDU5000: The **SDU-5000** Spectrum Display Unit adds a variety of features to extend a receiver's capabilities, such as visually identifying new active frequencies and taking measurements. The SDU-5000 may be used with a number of receivers which have a 10.7 MHz I.F. output and produces a bandwidth up to ± 5 MHz in 1 kHz increments with a resolution of 5 kHz or 30 kHz. The SDU-5000 remains compact due to the use of an internal 3.1" HQM simple matrix 16 colour LCD 192 dot x 210 dot. An external home colour television with video input may also be connected (PAL or NTSC). In particular the AR3000A has been designed to provide best compatibility by communicating directly via the receiver's CPU via the RS232 port / SDU-5000 COM1 ensuring the full potential of the SDU may be exploited.


Tape recorder compatibility

This custom modification enables the AR3000A to provide better compatibility with a range of off the shelf tape recorders. The receiver uses a pair of Darlington transistors for tape motor On/Off control. While this is suitable for many machines, some require independent relay contacts.

The modification consists of a small internally fitted double pole slave relay driven by the switching transistors. One pair of relay contacts feed back to the AUX socket via a 10 OHM resistor (to prevent relay sticking) and provides independent relay contacts not referenced to ground. The second pair of contacts feed audio to the AUX socket when the squelch is open with a high value resistor preventing noise pick-up when the contact is open. Constant audio is still fed to another pin of the AUX socket taken from a point before the relay (audio is permanently fed so that commercial users may decode CTCSS signals without encountering any squelch rise time). This makes the tape output modification ideally suited for direct DC switching of tape motors (not mains!) and for voice activated systems.

Discriminator output

This custom modification provides an output to the rear panel AUX socket taken directly from the FM MC3357 IC. This ensures the best compatibility with specialist data receivers used on the VHF bands for decoding pagers etc.



AR3000A PLUS

now available to order, please call for current price.